



AR NEWS

31th issue, October 2015, Allresist GmbH

Content:

- 1. Innovative new developments presented on the MNE 2015 and the SEMICON Europe: A case for two – CSAR 62 & Electra 92**
- 2. Alternative to Espacer Electra 92 meets user expectations**
 - 2.1 Long shelf life of Electra 92
 - 2.2 CSAR structures on glass, made possible due to Electra 92
 - 2.3 PMMA lift-off structures on semi-precious stone substrates with Electra 92
 - 2.4 Electra 92 for applications on novolac-base resists -
New variant SX AR-PC 5000/91.1 for negative CAR AR-N 7700 on glass
- 3. Allresist turns 23 years old and rejuvenates**



Welcome to the 31st issue of AR NEWS. Once again, we would like to inform you about the further development of the company and our research projects.

1. Innovative new developments presented on the MNE 2015 and the SEMICON Europe: A case for two – CSAR 62 & Electra 92

Allresist presented with great public attention the two new developments CSAR 62 and Electra 92 on the MNE (Micro and Nano Engineering) in The Hague in September 2015 and on the SEMICON Europe in Dresden in October.

For excellent results in electron beam lithography on glass or other insulating substrates, the interplay between both resists is indispensable – simply a case for two – and many visitors to our exhibition booths were impressed with the recent results concerning this perfect match. Both events turned out to be very successful for us and in many respects reflect our current financial year. Our sales volumes have increased further, at an export share of meanwhile 39 %. Two important scientific projects are still in progress; three further projects are shortly before approval. The hot summer in addition brought us high electrical power yields from our new photovoltaic system with monthly energy feeds of 3500 kWh into the public grid.




Fig. 1: Allresist exhibition booth on the MNE in The Hague

2. Alternative to Epcacer Electra 92 meets user expectations

2.1 Long shelf life of Electra 92

A long product shelf life is always important for users. To assess the storage stability, two Electra batches were subjected to conductivity measurements after different storage times (15 months and 3 months, respectively). The studies demonstrated that the determined conductivities of both samples on quartz are almost identical up to 100 °C. These results indicate a constant conductivity and thus a high storage stability even after 15 months of storage.




Fig. 2: Conductivity properties of Electra 92 batches stored for different times

Interesting to note is also that raising the temperature to more than 160 °C leads to a drastic increase in conductivity. This increase is mainly caused by the removal of water from the resist layer. After cooling to room temperature, the conductivity decreases again within several hours which can be explained by a reabsorption of water from the humidity in the air. If the layer is heated to more than 165 °C and thus the decomposition temperature is reached, the conductivity decreases abruptly and irreversibly.

2.2 CSAR structures on glass, made possible due to Electra 92

The use of a combination of CSAR 62 and the conductive coating Electra 92 in e-beam lithography allows the manufacture of highly complex structures on insulating glass or semi-insulating substrates such as e.g. gallium arsenide. The very high sensitivity and excellent resolution of CSAR 62 are harmoniously complemented by the good conductive properties of Electra 92.




Fig. 3: 30 – 150 nm squares of CSAR 62 on glass, supported by Electra 92 (SX AR-PC 5000/90.2)

The process parameters are listed in detail in the product description of Electra 92 and can be accessed at any time.

2.3 PMMA lift-off structures on semi-precious stone substrates with Electra 92

Semi-precious stones like sapphire or garnet increasingly gain in importance as substrates for semiconductor industry. Even though these materials have insulating properties, a patterning with electron beam lithography is nevertheless possible with the help of Electra 92. Mr. Chi Tang in the working group of Prof. Jing Shi at the University of California has been working with Electra 92 since six months. His special field of work is the coating of PMMA on semi-precious stones such as garnet in PMMA two-layer processes. Since he has started to work with SX AR-PC 5000/90.2, he is able to easily process his lift-off structures with the two-layer system.




Fig. 4: Lift-off structures on garnet, supported by Electra 92

All in all, a lot of praise came from our users who confirm that Electra 92 is at least equivalent to Spacer with respect to its specific properties. The adhesion features are even better, as the example of HSQ shows, and Electra 92 has furthermore a significantly longer shelf life. Another advantage is the price: Electra 92 is currently approximately 4 times cheaper and immediately available in variable pack sizes of 30 ml, 100 ml, and 250 ml up to 1 litre. 30 ml test samples are even offered at half price.

2.4 Electra 92 for applications on novolac-base resists - New variant SX AR-PC 5000/91.1 for negative CAR AR-N 7700 on glass

Novolac-based e-beam resists have other surface properties than e.g. CSAR 62, PMMA, or HSQ resists. Since September 2015, also a second version of Electra with the experimental sample designation SX AR-PC 5000/91.1 is available on the market which specifically and reliably works on novolac-based e-beam resists (e.g. AR-N 7500, 7700). This version is characterised by identical polymer properties, contains however a modified solvent mixture which exhibits improved coating properties on novolac-based resist layers.

With this second version of Electra, the novolac-based e-beam resist AR-N 7700.08 could be processed on quartz with a resolution of 60 nm, which is a good resolution for a chemically amplified resist:




Fig. 5: 60 – 150 nm squares of AR-N 7700.08 (100 nm height) on glass

3. Allresist turns 23 years old and rejuvenates

Today, on 16 October 2015, Allresist celebrates its 23rd company anniversary. We think that this event has deserved a few more news:

The 28 year-old Ulrike Dorothea Schirmer who has been working since 2011 at Allresist during her studies and is now partner since this year, will follow in the footsteps of her parents and become managing director in approximately 10 years. The continuity of Allresist is thus secured until the year 2054, and framework agreements until then are more than welcome 😊.

In her successfully completed studies as film producer, she has already demonstrated her over-average organizational and leadership talents. This is also reflected by her nomination for the Germany-wide "First Step Award" of the film industry as producer.

She will in addition shortly begin extra occupational distance studies in order to be able to control the future destinies of Allresist in two years even better as new Master of Management and Business Administration.

The second new addition to strengthen the team is the employment of Dr. Maik Gerngroß, a 31-year-old graduate chemist. With this decision, Allresist responded to the growing number of customers and scientific projects. The focus of his

activities is on sales responsibilities, customer service and project management, but he will also contribute to new product developments. Gerngroß is a flexible team player, innovative, enthusiastic, creative and able to work well under stress. Please challenge him.

The pictures show both of them before and after their first Strausberg half-marathon with the Allresist jersey „Mit Allresist läuft's ".

For any future applications, we would in fact greatly appreciate half marathon times of less than 2:13 h for women and less than 1:46 h for men 😊.



Fig. 9: Allresist staff member Ulrike Dorothea Schirmer and Maik Gerngroß ready to run

We hope that you could find new ideas and inspiration in our report and encourage you to address your particular wishes to us.

The next issue of our AR NEWS will again be presented in April 2016.
Successful times until then!



Strausberg, 16.10.2015
Matthias & Brigitte Schirmer
Team of Allresist